Product datasheet

Specifications





(!) Discontinued

die-cast empty control station -XAPM - Ø22 - zinc alloy - 3 horizontal openings

Local distributor code: 393523317

XAPM3503

() Discontinued on: 18 Apr 2024

EAN Code: 3389110313079

Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	ХАРМ					
Product Destination	For Ø 22 mm control and signalling units					
Product Front Plate Size	80 x 175 mm					
Usable Depth	74.5 mm					
Number Of Cut-Out	3 cut-outs					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Zinc alloy					
Cable Entry	1 hole with blanking plug for cable gland, clamping capacity: 18 mm 1 hole without blanking plug for cable gland, clamping capacity: 18 mm					
Device Mounting	Flush					
Ip Degree Of Protection	IP65 conforming to IEC 60529					

Complementary

Number Of Vertical Rows	1				
Net Weight	1145 kg				

Environment

Protective Treatment	ТС					
Ambient Air Temperature For Storage	-4070 °C					
Ambient Air Temperature For Operation	-4070 °C					
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030					

Packing Units

Unit Type Of Package 1	PCE				
Number Of Units In Package 1	1				
Package 1 Height	8.5 cm				
Package 1 Width	12 cm				

Package 1 Length	18.5 cm	
Package 1 Weight	1.298 kg	

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

Product datasheet

Dimensions Drawings

Dimensions and Fixing



(1) 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 118 mm/0.71 in. maximum clamping capacity

- (3) $2 \times \emptyset 5.6 \text{ mm}/0.22 \text{ in. holes, depth } 20 \text{ mm}/0.78 \text{ in.}$
- P Usable depth

а		b		С		G		Н		Р		
	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
	80	3.15	175	6.89	77	3.03	50	1.97	160	6.30	74.5	2.93

Refer to the product characteristics to get the number of cut-outs. **Cut-out interaxis dimensions**



b1 Vertical interaxis: 40 mm/1.57 in.