







Pack 22mm XB5R programble receiver AC/DC

Local distributor code: 398126463

XB5RFA02

EAN Code: 3606480334450

Main

Range Of Product	Harmony XB5R
Product Or Component Type	Wireless and batteryless package
Device Short Name	XB5R
Head Material	Plastic
Frequency	2405 MHz for transmitter 2405 MHz for receiver
Emission Class	5M00G7W
Antenna Type	Omnidirectional

Complementary

Control Type	Wireless and batteryless push-button Ø 22 mm assembled on fixing collar	
Type Of Receiver	Programmable receiver (2 relays)	
[Us] Rated Supply Voltage	24240 V AC/DC 50/60 Hz	
Kit Composition	1 transmitter 1 set of caps 1 receiver 1 fixing collars 1 diameter: 22 mm 1 push-button head diameter: 22 mm	
Status Led	1 LED green for power ON 2 LEDs green for relay ON 2 LEDs green for function mode 1 LED green and yellow for reception signal	
Communication Port Protocol	Zigbee conforming to IEEE 802.15.4	
Max Power Consumption In W	1 mW	
Number Of Channels	1	
Modulation Technique	O-QPSK	
Bandwidth	5 MHz	
Antenna Gain	0 dBi	
Customizable	No	
Compatibility Code	XB5R	

Environment

Product Certifications	UL	
	CCC	
	GOST	
	CSA	
	C-Tick	

Marking	CE	
Standards	CSA C22.2 No 14	
	IEC 60947-5-1	
	UL 508	
	IEC 60947-1	
Radio Agreement	SRRC	
	RSS	
	ARIB T66	
	FCC	
	ICASA	
	ANATEL	

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.300 cm
Package 1 Width	10.500 cm
Package 1 Length	10.800 cm
Package 1 Weight	207.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.850 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

XB5RFA02

Dimensions Drawings

Programmable Receiver







XB5RFA02

Wireless and Batteryless Pushbutton - Transmitter

With Plastic Pushbutton without Cap






e: panel thickness 1 to 6 mm / 0.039 to 0.24 in.

XB5RFA02


Mounting and Clearance

Receiver Clearance




- (1) Drive
- (2) Power Supply or PLC

Receiver Mounting



Connections and Schema

Programmable Receiver



- (1) 500 mA
- (2) Output contacts
- (3) Imax = 3 A