Product datasheet

Specifications





die-cast empty control station -XAPM - Ø 22 - zinc alloy - 4

openings Local distributor code: 2201328

XAPM2204H29

() Discontinued on: 29 Sept 2022

(!) Discontinued

EAN Code: 3389118115538

М	ai	n
	a	

Range Of Product	Harmony XAP
Product Or Component Type	Die-cast empty control station
Device Short Name	ХАРМ
Product Destination	For Ø 22 mm control and signalling units
Product Front Plate Size	80 x 130 mm
Usable Depth	49 mm
Number Of Cut-Out	4 cut-outs
Colour Of Base Of Enclosure	Blue
Colour Of Cover	Blue
Material	Zinc alloy
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland, clamping capacity: 20 mm 1 hole without blanking plug for ISO 429248 cable gland, clamping capacity: 20 mm
Device Mounting	Flush
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP69 conforming to NF C 20-010 IP69K

Complementary

Number Of Vertical Rows	2
Net Weight	0.6 kg

Environment

Protective Treatment	тс		
Ambient Air Temperature For Storage	-4070 °C		
Ambient Air Temperature For Operation	-4070 °C		
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm

Package 1 Width	9.5 cm
Package 1 Length	15.5 cm
Package 1 Weight	695.9 g

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Dimensions and Fixing



(1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity

- (3) $2 \times \emptyset 5.6 \text{ mm}/0.22 \text{ in. holes, depth } 20 \text{ mm}/0.78 \text{ in.}$
- P Usable depth

а		b		с		G		Н		Р		
	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
	80	3.15	130	5.12	51.5	2.03	50	1.97	115	4.53	49	1.93

Refer to the product characteristics to get the number of cut-outs. **Cut-out interaxis dimensions (vertical mounting)**



- b1 Vertical interaxis: 40 mm/1.57 in.
- b2 Horizontal interaxis: 30 mm/1.18 in.