Product datasheet

Specifications

 → Green Premium[™]



empty control station - XAP-M - zinc alloy - without opening

Local distributor code: 22489049

XAPM24H29

Discontinued on: 14 Jun 2022

(!) End-of-service on: 30 Jun 2022

EAN Code: 3389118115521

Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	XAPM					
Product Front Plate Size	80 x 130 mm					
Usable Depth	74.5 mm					
Number Of Cut-Out	Undrilled					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Zinc alloy					
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland, clamping capacity: 20 mm 1 hole without blanking plug for ISO 429248 cable gland, clamping capacity: 20 mm					
Product Mounting	Flush mounting					
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP69 conforming to NF C 20-010 IP69K					

Complementary

Net Weight

0.83 kg

Environment

Protective Treatment	тс				
Ambient Air Temperature For Storage	-4070 °C				
Ambient Air Temperature For Operation	-4070 °C				
Electrical Shock Protection Class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	8.8 cm
Package 1 Length	15.5 cm

Package 1 Weight

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

Dimensions Drawings

Dimensions and Fixing



(1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.24 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	130	5.12	77	3.03	50	1.97	115	4.53	74.5	2.93

(3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.