



! Discontinued

empty control station - XAP-M - aluminium alloy - 8 openings

XAPM5508H29

! Discontinued on: 1 Oct 2020

EAN Code: 3389118115309

Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	XAPM					
Product Destination	For Ø 22 mm control and signalling units					
Product Front Plate Size	85 x 310 mm					
Usable Depth	74.5 mm					
Number Of Cut-Out	8 cut-outs					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
	Aluminium alloy					
Cable Entry	1 hole without blanking plug for ISO 429248 cable gland, clamping capacity: 32 mm					
Ip Degree Of Protection	IP65 conforming to IEC 60529					

Complementary

Number Of Vertical Rows	1
Net Weight	0.81 kg

Environment

Protective Treatment	тс				
Ambient Air Temperature For Storage	-4070 °C				
Ambient Air Temperature For Operation	-4070 °C				

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	End of Life Information					

Dimensions Drawings

Dimensions and Fixing



- (1) 1 hole, without blanking plug, for cable gland with 24 mm/0.94 in. maximum clamping capacity
- (3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.
- P Usable depth

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
85	3.35	310	12.20	77	3.03	55	2.17	295	11.61	74.5	2.93

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions



b1 Vertical interaxis: 30 mm/1.18 in.