# **Product datasheet**





# module XPSAR - Emergency stop - 115 V AC

Local distributor code: 407169081

XPSAR351144

! Discontinued on: 3 Jul 2021

EAN Code: 3389110274288

① Discontinued

## Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSAR
Safety Module Application	For emergency stop, switch and safety light curtain monitoring
Function Of Module	Monitoring of a movable guard Monitoring of a movable guard associated with 2 switches and automatic start Emergency stop with 2 NC contacts monitoring 2-channel wiring Multiple emergency stop monitoring 2-channel wiring Monitoring of electro-sensitive protection equipment (ESPE) Emergency stop monitoring 1-channel wiring
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061
Safety Reliability Data	DC > 99 % conforming to EN/ISO 13849-1 MTTFd = 277.8 years conforming to EN/ISO 13849-1 PFHd = 2.22E-9 1/h conforming to EN/IEC 62061
Type Of Start	Configurable
Connections - Terminals	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² solid with cable end, with double bezel Captive screw clamp terminals, 1 x 0.251 x 1.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 1 x 0.251 x 2.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² solid with cable end, with double bezel Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.252 x 1 mm² flexible with cable end, with double bezel Captive screw clamp terminals, 2 x 0.52 x 1.5 mm² flexible with cable end, with double bezel
Output Type	Relay instantaneous opening, 7 NO circuit(s), volt-free
Number Of Additional Circuits	2 NC + 4 solid state outputs
[Us] Rated Supply Voltage	115 V AC - 1510 %

## Complementary

Complementary	
Synchronisation Time Between Inputs	100 ms
Supply Frequency	50/60 Hz
Maximum Power Consumption In W	4 W DC
Maximum Power Consumption In Va	9 VA AC

24 V DC - 15...10 %

Life Is On Schneider 23 Apr 2024

Input Protection Type	Internal, electronic
[Uc] Control Circuit Voltage	24 V DC
Maximum Line Resistance	50 Ohm
Breaking Capacity	360 VA holding AC-15 C300 relay output 3600 VA inrush AC-15 C300 relay output
Breaking Capacity	20 mA at 24 V 2 A at 24 V (DC-13) time constant: 50 ms for relay output
Output Thermal Current	10 A per relay for relay output
[Ith] Conventional Free Air Thermal Current	40 A
Associated Fuse Rating	10 A fast blow for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A gG or gL for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum Output Current	170 mA for relay output
Minimum Output Voltage	17 V for relay output
Maximum Response Time On Input Open	20 ms
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local Signalling	4 LEDs
Current Consumption	20 mA at 24 V DC on power supply
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.4 kg

## **Environment**

Standards	EN/IEC 60947-5-1 EN/IEC 60204-1 EN/ISO 13850 EN 1088/ISO 14119
Product Certifications	CSA UL TÜV
Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-1055 °C
Ambient Air Temperature For Storage	-2585 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.45 cm
Package 1 Width	10.92 cm
Package 1 Length	10.41 cm
Package 1 Weight	0.71 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	12

Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9.075 ka

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

## **Certifications & Standards**

Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

# **Product datasheet**

## XPSAR351144

## **Dimensions Drawings**

#### **Dimensions**

