



safety controller XPS-MC - 24 V DC - 16 input - 32 LEDs signalling

XPSMC16ZPPACK

EAN Code: 3389119018272

! Discontinued

Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Kit configurable safety controller
Safety Module Name	XPSMC
Safety Use Category	Category 4 maximum conforming to EN 954-1/EN/ISO 13849-1 PLE maximum conforming to EN/ISO 13849-1 SIL 3 maximum conforming to IEC 61508
Type Of Start	Configurable
Standards	IEC 61508 EN/IEC 60947-5-1 EN/IEC 60204-1 EN/IEC 61496-1 EN 954-1/EN/ISO 13849-1 EN 1760-1/ISO 13856-1 EN 574/ISO 13851
Product Certifications	TÜV CSA UL
[Us] Rated Supply Voltage	24 V DC - 2020 %
Number Of Inputs	16
Communication Port Protocol	Modbus with 1 RJ45 port(s), serial link, transmission rate: 1200 bps, 2400 bps, 4800 bps, 9600 bps or 19200 bps Profibus with 1 SUB-D 9-pin female port(s), serial link, transmission rate: 12 Mbps
Safety Level	Can reach PL e/category 4 conforming to EN 954-1/EN/ISO 13849-1 Can reach SIL 3 conforming to IEC 61508

Complementary

Kit Composition	Safety controller
	Set of screw terminals
	Connection cable
	Printed packaging label 80 x 50 mm
	Configuration software
	LISR/DS495 convertor

USB/RS485 converter
Profibus connectors
Set of cage clamp terminals
VDE slot screwdriver 2.5 x 75 mm

Packaging small model for software configuration

Ethernet cable 2m

Function Of Module	Dynamic monitoring of hydraulic valves on linear presses
	Eccentric press
	Emergency stop monitoring, with or without time delay, 1 or 2-channel wiring Enabling switch monitoring, 2 or 3 contacts
	Foot switch monitoring
	Guard monitoring for injection presses and blowing machines
	Guard monitoring with 1 or 2 limit switches
	Hydraulic press Magnetic switch monitoring
	Monitoring safety stop at top dead centre on eccentric press
	Muting function of light curtains
	Position selector
	Safety mat monitoring
	Safety time delays Shaft/chain breaking monitor
	Zero speed detection
	Light curtain monitoring category 4 conforming to EN/IEC 61496
	Two-hand control category 3 conforming to EN 574/ISO 13851
Synchronisation Time Between Inputs	Depending on configuration selected
Power Consumption In W	12 W
Input Protection Type	External fuse 16 A
[Uc] Control Circuit Voltage	28.8 V
Maximum Line Resistance	100 Ohm <2000 m
Output Type	2 relays, 2 NO contacts (4 NO total) circuit(s)
	Solid state, 6 circuit(s), volt-free
Bus altimu Come attra	
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking Capacity	2 A at 24 V for static output circuit 1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Output Thermal Current	4 A for both outputs simultaneously 6 A for 1 output and 2 A for the other for relay output
[Ith] Conventional Free Air	16 A for relay output
Thermal Current	6.5 A for static output circuit
Associated Fuse Rating	16 A gL for power supply
3	4 A gL for relay output
	6 A fast blow for relay output
Minimum Output Current	10 mA for relay output
Minimum Output Voltage	17 V for relay output
Response Time	Configurable : 20 ms or 30 ms with software XPSMCWIN
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60647-5-1, DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60647-5-1, DIN VDE 0110 part 1
Method Of Access	Slave
Exchange Size	14 words
Number Of Addresses	1125 for Profibus 1247 for Modbus
Parity	Even for Modbus
-	No for Modbus
	Odd for Modbus
Data Format	1 start hit/9 data hits
Jam Format	1 start bit/8 data bits 1 stop bit even or odd
	2 stop bits without parity
	RTU (Remote Terminal Unit) mode
Supported Modbus Function	04: 9 hit output data/32 hit input data
Oupported Mounus FullCuoli	01: 8-bit output data/32-bit input data 02: 32-bit input data/8-bit output data
	03: information and errors
Local Signalling	32 LEDs

Mounting Support	Mounting plate
Depth	153 mm
Height	151.5 mm
Width	74 mm
Net Weight	0.82 kg

Environment

Ip Degree Of Protection	IP20 conforming to EN/IEC 60529	
Ambient Air Temperature For Operation	-1055 °C	
Ambient Air Temperature For Storage	-2585 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25 cm
Package 1 Width	25 cm
Package 1 Length	27.5 cm
Package 1 Weight	2.466 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards


Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

Product datasheet

XPSMC16ZPPACK

Dimensions Drawings


Dimensions



When using XPSMCTS• connectors this dimension is 153 mm (6.02 in)
When using XPSMCTC• connectors this dimension is 151,5 mm (5.96 in)

Mounting and Clearance

Installation



Metal adaptor for fixing on metal: DIN rail 35 mm/1.38 in.

Product datasheet

XPSMC16ZPPACK

Connections and Schema


Wiring Diagrams

Refer to the Instruction Sheet

To download the instruction sheet, follow below procedure:



XPSAC5121 module XPSAC - Emergency stop - 24 V AC DC Download XPSAC5121 product datasheet



- 1 Click on Download & Documents.
- 2 Click on Instruction sheet.

XPSMC16ZPPACK

Technical Description

Safety Functions

 Emergency stop monitoring with time delay: 1 channel wiring, with automatic start. 2 channel wiring, with start button.
 Emergency stop monitoring without time delay: 1 channel wiring, with automatic start. 2 channel wiring, with start button.
• Two-hand control.
Guard monitoring: with 1 limit switch. with 2 limit switches. with 2 limit switches, with guard locking. Guard monitoring for injection presses and blowing machines.
• Magnetic switch monitoring.

Product datasheet XPSMC16ZPPACK

	• Sensing mat monitoring.
9	 Light curtains monitoring: Relay output type. Solid-state output type. "Muting" function for light curtains.
	• Zero speed detection.
	 Dynamic monitoring of hydraulic valves on linear presses.
	• Safety time delays.
	 Monitoring safety stop at top dead centre on eccentric press. Hydraulic press. Eccentric press.

Product datasheet

XPSMC16ZPPACK



- Enabling switching monitoring:
 - 2 contact type.3 contact type.

Other functions:

- Foot switch monitoring
- Chain shaft breakage monitoring
- Position selector