Product datasheet

Specification





Pilot light, Harmony XB4, white complete Ø22 mm plain lens with BA9s bulb 110...120 V

Local distributor code: 409066221 XB4BV31

EAN Code: 3389110887211

Main

Range Of Product	Harmony XB4			
Product Or Component Type	Pilot light			
Device Short Name	XB4			
Bezel Material	Chromium plated metal			
Fixing Collar Material	Zamak			
Head Type	Standard			
Mounting Diameter	22.5 mm			
Sale Per Indivisible Quantity	1			
Shape Of Signaling Unit Head	Round			
Cap/Operator Or Lens Colour	White			
Operator Additional Information	With plain lens			
Light Source	Incandescent			
Bulb Base	BA 9s			
Light Block Supply	Via integral transformer 1.2 VA 6 V			
[Us] Rated Supply Voltage	110120 V AC at 50/60 Hz			

Complementary

Height	47 mm				
Width	30 mm				
Depth	78 mm				
Terminals Description Iso N°1	(X1-X2)PL				
Net Weight	0.152 kg				
Resistance To High Pressure Washer	7000000 Pa at 55 °C, distance : 0.1 m				
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end conforming to IEC 60947-1 Screw clamp terminals, 1 x 0.222 x 2.5 mm² without cable end conforming to IEC 60947-1				
[Ui] Rated Insulation Voltage	600 V (pollution degree 3) conforming to IEC 60947-1				
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1				
Signalling Type	Steady				

Environment

Protective Treatment	тн				
Ambient Air Temperature For Storage	-4070 °C				
Ambient Air Temperature For Operation	-4055 °C				
Electrical Shock Protection Class	Class I conforming to IEC 60536				
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K				
Nema Degree Of Protection	NEMA 13 NEMA 4X				
Ik Degree Of Protection	IK06 conforming to IEC 50102				
Standards	IEC 60947-5-4 IEC 60947-5-5 IEC 60947-5-1 UL 508 JIS C8201-5-1 IEC 60947-1 CSA C22.2 No 14 JIS C8201-1				
Product Certifications	UL listed CSA				
Vibration Resistance	5 gn (f= 12500 Hz) conforming to IEC 60068-2-6				
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	5.2 cm
Package 1 Length	8.2 cm
Package 1 Weight	145.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.8 cm
Package 2 Width	3.4 cm
Package 2 Length	26.5 cm
Package 2 Weight	728.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	50
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	7.741 kg

Contractual warranty

Warranty

25 Apr 2024

18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			
Circularity Profile	End of Life Information			

25 Apr 2024

XB4BV31

Dimensions Drawings

Dimensions



e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

a in mm	a in in.	b in mm	b in in.	c in mm	c in in.		
66	2.60	30	1.18	46.5	1.83		


XB4BV31

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connectors or on Printed Circuit Board (1)(2)

Connection by Screw Clamp Terminals or Plug-in



Connection by Faston Connectors

(1) Diameter on finished panel or support

(3)

- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0^{+0.4}$ / 0.88 in. $_0^{+0.016}$)

(4)

- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.