

# Product datasheet

Specifications



## 60mm Tower ROGB Base Mount

Local distributor code:

403035504

XVC6B5K

⚠ Discontinued on: 7 Aug 2023

EAN Code: 3606480032639

⚠ Discontinued

### Main

Range Of Product	Harmony XVC6
Product Or Component Type	Complete pre-wired monolithic tower light
Beacon Or Indicator Bank Unit Type	5 illuminated units
Sound Signalling	Without
Mounting Diameter	60 mm
Component Name	XVC
Light Source	LED steady red LED steady orange LED steady green LED steady blue LED steady clear
[Us] Rated Supply Voltage	24 V
Supply Circuit Type	AC/DC

### Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover
Product Mounting	On base
Cable Cross Section	0.33 mm²
Awg Gauge	AWG 22
Cable Length	850 mm
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	125 mA
Flashing Frequency	1 Hz
Net Weight	0.4 kg
Height	280.8 mm

### Environment

Standards	EN/IEC 61000-6-2 EN/IEC 61000-6-4 EN/IEC 61000-6-3
Product Certifications	UL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-10...50 °C
Electrical Shock Protection Class	Class II conforming to EN/IEC 61140
Ip Degree Of Protection	IP54 flat surface installation conforming to EN/IEC 60529

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.6 cm
Package 1 Length	50.0 cm
Package 1 Weight	562.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	7.656 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance


✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	<a href="#">China RoHS declaration</a>	
Environmental Disclosure	<a href="#">Product Environmental Profile</a>	
Circularity Profile	<a href="#">End of Life Information</a>	

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



No. of illuminated units	b (mm)	b (in.)
1 stage	120.8	4.76
2 stages	160.8	6.33
3 stages	200.8	7.90
4 stages	240.8	9.48
5 stages	280.8	11.06

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

