

Product datasheet

Specifications



60mm Tower ROGBC Pole 100-240VAC

XVC6M5

⚠ Discontinued on: 1 Jul 2020

EAN Code: 3606480072598

⚠ Discontinued

Main

Range Of Product	Harmony XVC6
Product Or Component Type	Complete pre-wired monolithic tower light
Beacon Or Indicator Bank Unit Type	5 illuminated units
Sound Signalling	Without
Mounting Diameter	60 mm
Component Name	XVC
Light Source	LED steady red LED steady orange LED steady green LED steady blue LED steady clear
[Us] Rated Supply Voltage	100...240 V
Supply Circuit Type	AC

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94-V0): top cover
Product Mounting	On support tube, 22 mm
Cable Cross Section	0.33 mm ² 0.83 mm ²
Awg Gauge	AWG 22 AWG 18
Cable Length	550 mm 450 mm
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	4 kV
Current Consumption	90 mA
Net Weight	1.18 kg
Height	759.8 mm

Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60947-1
Product Certifications	UL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-10...50 °C
Electrical Shock Protection Class	Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP23 vertical surface installation conforming to EN/IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	8.5 cm
Package 1 Length	77.5 cm
Package 1 Weight	1.472 kg
Unit Type Of Package 2	S06
Number Of Units In Package 2	1
Package 2 Height	73.5 cm
Package 2 Width	60.0 cm
Package 2 Length	80.0 cm
Package 2 Weight	14.472 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	18
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	34.996 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile


[End of Life Information](#)

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b1** dimension.



No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	599.8	23.61
2 stages	639.8	25.19
3 stages	679.8	26.76
4 stages	719.8	28.34
5 stages	759.8	29.91

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting

