Product datasheet

Specifications





Illuminated unit for modular tower lights, plastic, yellow, Ø70, integral "flash" discharge tube, 5 joule, 24 V AC/DC

Local distributor code:

380608685 XVBC6B8

EAN Code: 3389110845655

Main

| Range Of Product | Harmony XVB Universal | |
|---------------------------------------|---------------------------------------|--|
| Product Or Component Type | Indicator bank | |
| Beacon Or Indicator Bank Unit Type | Illuminated unit | |
| Signalling Type | Flashing | |
| Mounting Diameter | 70 mm | |
| Component Name | XVBC | |
| Material | Polycarbonate | |
| Light Source | Integral flash discharge tube, yellow | |
| Bulb Type | Flash discharge tube | |
| [Us] Rated Supply Voltage | 24 V AC/DC | |
| Flash Energy | 5 J | |

Complementary

| Assembly Style | Customer assembly, up to 5 units | |
|--|--|--|
| Connections - Terminals | Screw clamp terminals, <= 1 x 1.5 mm² with cable end | |
| [Ui] Rated Insulation Voltage | 250 V conforming to IEC 60947-1 | |
| Nominal Voltage Limit | 0.851.1 Un conforming to IEC 60947-5-1 | |
| Current Consumption | < 350 mA DC < 550 mA AC | |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV conforming to IEC 60947-1 | |
| Flashing Frequency | 1 Hz | |
| Cad Overall Width | 70 mm | |
| Cad Overall Height | 157 mm | |
| Cad Overall Depth | 70 mm | |
| Net Weight | 0.295 kg | |

Environment

| Product Certifications | CCC EAC CSA C22-2 No 14 UL 508 |
|------------------------|---|
| Standards | IEC 60947-5-1 |
| Protective Treatment | TC |

| Ambient Air Temperature For Storage | -4070 °C |
|--|---|
| Electrical Shock Protection Class | Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140 |
| Ip Degree Of Protection | IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529 |
| Nema Degree Of Protection | Type 4X conforming to UL (indoor) |

Packing Units

| PCE |
|----------|
| 1 |
| 8 cm |
| 9.8 cm |
| 21.6 cm |
| 296 g |
| S03 |
| 12 |
| 30 cm |
| 30 cm |
| 40 cm |
| 4.027 kg |
| |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |


XVBC6B8

Dimensions Drawings

Indicator Bank with "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get \mathbf{b} dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC•••, to be ordered separately
- (3) "Flash" unit

| Number of illuminated or audible signalling units other than "flash" tube | | b in in. |
|---|-----|----------|
| 1 | 295 | 11.61 |
| 2 | 358 | 14.09 |
| 3 | 421 | 16.57 |
| 4 | 484 | 19.06 |