# **Product datasheet**

Specification





Illuminated unit for modular tower lights, plastic, orange, Ø70, integral "flash" discharge tube, 5 joule, 230 V AC

XVBC6M5

Local distributor code: 380654930

EAN Code: 3389110845860

### Main

mam		
Range Of Product	Harmony XVB Universal	
Product Or Component Type	Indicator bank	
Beacon Or Indicator Bank Unit Type	Illuminated unit	
Signalling Type	Flashing	
Mounting Diameter	70 mm	
Component Name	XVBC	
Material	Polycarbonate	
Light Source	Integral flash discharge tube, orange	
Bulb Type	Flash discharge tube	
[Us] Rated Supply Voltage	230 V AC	
Flash Energy	5 J	

## Complementary

Assembly Style	Customer assembly, up to 5 units	
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end	
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1	
Nominal Voltage Limit	0.851.1 Un conforming to IEC 60947-5-1	
Current Consumption	< 105 mA AC	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1	
Flashing Frequency	1 Hz	
Cad Overall Width	70 mm	
Cad Overall Height	157 mm	
Cad Overall Depth	70 mm	

### **Environment**

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508	
Standards	IEC 60947-5-1	
Protective Treatment	тс	
Ambient Air Temperature For Storage	-4070 °C	

<b>Electrical Shock Protection Class</b>	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140
Ip Degree Of Protection	IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529
Nema Degree Of Protection	Type 4X conforming to UL (indoor)

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	8.000 cm
Package 1 Length	18.800 cm
Package 1 Weight	290.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.925 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations


## XVBC6M5

#### **Dimensions Drawings**

### Indicator Bank with "Flash" Discharge Tube Unit

#### **Dimensions**

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get  $\mathbf{b}$  dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC•••, to be ordered separately
- (3) "Flash" unit

Number of illuminated or audible signalling units other than "flash" tube		b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06