



pushbutton head for harsh environment - dark blue - with marking

ZB4BC68026

! Discontinued on: 1 Jul 2020

! Discontinued

EAN Code: 3606480444715

Main

Range Of Product	Harmony XB4	
Product Or Component Type	Head for push-button	
Device Short Name	ZB4	
Bezel Material	Chromium plated metal	
Head Type	Standard	
Mounting Diameter	22 mm	
Sale Per Indivisible Quantity	1	

Complementary

Cad Overall Width	37 mm	
Cad Overall Height	18.5 mm	
Cad Overall Depth	37 mm	
Net Weight	0.036 kg	
Electrical Shock Protection Class	Class I conforming to IEC 61140	
Shape Of Signaling Unit Head	Init Head Round	
Type Of Operator	spring return	
Operator Profile	Blue flush, type H026 (white)	
Operator Additional Information	Vertical mounting	
Mechanical Durability	10000000 cycles	
Vibration Resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27	
Main Group	Harsh environment	
Group Of Product	Flush marked type H026	
Cap/Operator Or Lens Colour	Blue	
Marking	Type H026	
Colour Of Marking	White	
Electrical Composition Code	C1 for <9 contacts using single blocks in front mounting C2 for <9 contacts using single and double blocks in front mounting	

C11 for <3 contacts using single blocks in front mounting C15 for <1 contacts using single blocks in front mounting

Environment

Ambient Air Temperature For Storage	-4085 °C	
Ambient Air Temperature For Operation	-4070 °C	
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP69K IP67 IP69	
Nema Degree Of Protection	NEMA 4 conforming to UL 508 NEMA 13 NEMA 12	
Resistance To High Pressure Washer	90 Pa at 82.5 °C	
Ik Degree Of Protection	IK06 conforming to IEC 62262	
Standards	IEC 60947-1 IEC 60947-5-1 UL 508 CSA C22.2	
Product Certifications	UL CSA CE	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings


Dimensions



Mounting and Clearance


Installation on Flat Surface

Without Protective Guard



(1) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 $_0^{+0.016}$)

With Protective Guard




(1) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 $_0^{+0.016}$)

Product datasheet

ZB4BC68026

Technical Description

Marking Type H026



Electrical Composition Corresponding to Code C1



Electrical Composition Corresponding to Code C2



Product datasheet

ZB4BC68026

Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



Electrical Composition Corresponding to Code C15

1 N/O



1 N/C



1 N/O + N/C or 1 N/O + N/O or 1 N/C + N/C



Legend

Single contact



Double contact



Light block



Possible location

