Specifications





## Head for illuminated selector switch, Harmony XB4, metal, white handle, 22mm, universal LED, 2 positions, spring return Local distributor code:

237118914

ZB4BK1433

Important message: Viktig information: en förändring i utseendet kan observeras på produkten, men detta påverkar inte dess användning i termer av funktion och säkerhet. Detta gör den kompatibel med våra Universal LED-block EAN Code: 3389110890488

#### Main

Product Or Component Type   Head for illuminated selector switch     Product Compatibility   Universal LED     Device Short Name   ZB4     Bezel Material   Chromium plated metal     Head Type   Standard     Mounting Diameter   22.5 mm     Sale Per Indivisible Quantity   1     Shape Of Signaling Unit Head   Round     Type Of Operator   Right to left spring return     Operator Profile   Green standard handle     Operator Position Information   2 positions 90°					
Product Compatibility   Universal LED     Device Short Name   ZB4     Bezel Material   Chromium plated metal     Head Type   Standard     Mounting Diameter   22.5 mm     Sale Per Indivisible Quantity   1     Shape Of Signaling Unit Head   Round     Type Of Operator   Right to left spring return     Operator Profile   Green standard handle     Operator Position Information   2 positions 90°	Range Of Product	Harmony XB4			
Device Short Name   ZB4     Bezel Material   Chromium plated metal     Head Type   Standard     Mounting Diameter   22.5 mm     Sale Per Indivisible Quantity   1     Shape Of Signaling Unit Head   Round     Type Of Operator   Right to left spring return     Operator Profile   Green standard handle     Operator Position Information   2 positions 90°	Product Or Component Type	Head for illuminated selector switch			
Bezel Material   Chromium plated metal     Head Type   Standard     Mounting Diameter   22.5 mm     Sale Per Indivisible Quantity   1     Shape Of Signaling Unit Head   Round     Type Of Operator   Right to left spring return     Operator Profile   Green standard handle     Operator Position Information   2 positions 90°	Product Compatibility	Universal LED			
Head Type   Standard     Mounting Diameter   22.5 mm     Sale Per Indivisible Quantity   1     Shape Of Signaling Unit Head   Round     Type Of Operator   Right to left spring return     Operator Profile   Green standard handle     Operator Position Information   2 positions 90°	Device Short Name	ZB4			
Mounting Diameter 22.5 mm   Sale Per Indivisible Quantity 1   Shape Of Signaling Unit Head Round   Type Of Operator Right to left spring return   Operator Profile Green standard handle   Operator Position Information 2 positions 90°	Bezel Material	Chromium plated metal			
Sale Per Indivisible Quantity 1   Shape Of Signaling Unit Head Round   Type Of Operator Right to left spring return   Operator Profile Green standard handle   Operator Position Information 2 positions 90°	Head Type	Standard			
Shape Of Signaling Unit Head Round   Type Of Operator Right to left spring return   Operator Profile Green standard handle   Operator Position Information 2 positions 90°	Mounting Diameter	22.5 mm			
Type Of Operator Right to left spring return   Operator Profile Green standard handle   Operator Position Information 2 positions 90°	Sale Per Indivisible Quantity	1			
Operator Profile Green standard handle   Operator Position Information 2 positions 90°	Shape Of Signaling Unit Head	Round			
Operator Position Information 2 positions 90°	Type Of Operator	Right to left spring return			
	Operator Profile	Green standard handle			
Cap/Operator Or Lens Colour Green	Operator Position Information	2 positions 90°			
	Cap/Operator Or Lens Colour	Green			

## Complementary

29 mm					
29 mm					
43 mm					
0.037 kg					
7000000 Pa at 55 °C, distance : 0.1 m					
500000 cycles					
M3 for <4 contacts using single blocks in front mounting with integral LED M6 for <2 contacts using single blocks in front mounting with integral LED and transformer M10 for <2 contacts using single blocks in front mounting with integral LED M4 for <4 contacts using single and double blocks in front mounting with integral LED					
Basic element					

## Environment

Protective Treatment

ΤН

Ambient Air Temperature For Storage	-4070 °C				
Ambient Air Temperature For Operation	-4070 °C				
Overvoltage Category	Class I conforming to IEC 60536				
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K				
Nema Degree Of Protection	NEMA 13 NEMA 4X				
Ik Degree Of Protection	IK04 conforming to IEC 50102				
Standards	IEC 60947-5-1 UL 508 IEC 60947-5-5 CSA C22.2 No 14 IEC 60947-5-4 IEC 60947-1 JIS C8201-5-1 JIS C8201-1				
Product Certifications	UL listed LROS (Lloyds register of shipping) GL CSA BV DNV				
Vibration Resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6				
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27				

## **Packing Units**

U					
Unit Type Of Package 1	PCE				
Number Of Units In Package 1	1				
Package 1 Height	4.800 cm				
Package 1 Width	5.200 cm				
Package 1 Length	3.300 cm				
Package 1 Weight	41.000 g				
Unit Type Of Package 2	BB1				
Number Of Units In Package 2	5				
Package 2 Height	4.800 cm				
Package 2 Width	26.500 cm				
Package 2 Length	3.300 cm				
Package 2 Weight	207.000 g				
Unit Type Of Package 3	S03				
Number Of Units In Package 3	250				
Package 3 Height	30.000 cm				
Package 3 Width	30.000 cm				
Package 3 Length	40.000 cm				
Package 3 Weight	11.377 kg				

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


### **Dimensions Drawings**

#### Dimensions




Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)



#### Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


Panel Cut-outs (Viewed from Installer's Side)




**A:** 30 mm min. / 1.18 in. min. **B:** 40 mm min. / 1.57 in. min.

### Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min. B: 40 mm min. Dimensions in in.



**A:** 1.18 in. min. **B:** 1.57 in. min.


#### General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in: T1 + T2 = 0.3 mm max.

#### Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB4 BZ009: ± 2 30' (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ 006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB4 BZ079 fixing collar/pillar and its fixing screws:
  - $_{\circ}$  every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
    - o with each selector switch head (ZB4 BD•, ZB4 BJ•, ZB4 BG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



(1) Panel

(2) Printed circuit board


#### Mounting of Adapter (Socket) ZBZ 01•

- 1 2 elongated holes for ZBZ 006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ 01•
- 3 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ 01•


Dimensions An + 18.1 relate to the Ø 2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 holes for centring adapter ZBZ 01.

**Technical Description** 


Electrical Composition Corresponding to Code M3



Electrical Composition Corresponding to Code M4



Electrical Composition Corresponding to Codes M6 and P2



Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2



#### Legend

Single contact



Double contact



Light block




Possible location



#### Sequence of Contacts Fitted to 2-position Selector Switch Body

#### Position 315°





#### Position 45°



		Тор		_	
Push	Position	Bottom			
	Location	•	Left	$\otimes$	Right
	State		1		1
	N/O		closed		closed
Contacts	N/C		open		open