# **Product datasheet**

Specification





Head for illuminated selector switch, Harmony XB4, metal, red handle, 22mm, universal LED, 3 positions, left to center

Local distributor code:

237119188

ZB4BK1743

Important message: Viktig information: en förändring i utseendet kan observeras på produkten, men detta påverkar inte dess användning i termer av funktion och säkerhet. Detta gör den kompatibel med våra Universal LED-block EAN Code: 3389110891096

#### Main

| Range Of Product              | Harmony XB4                          |  |  |  |
|-------------------------------|--------------------------------------|--|--|--|
| Product Or Component Type     | Head for illuminated selector switch |  |  |  |
| Product Compatibility         | Universal LED                        |  |  |  |
| Device Short Name             | ZB4                                  |  |  |  |
| Bezel Material                | Chromium plated metal                |  |  |  |
| Head Type                     | Standard                             |  |  |  |
| Mounting Diameter             | 22.5 mm                              |  |  |  |
| Sale Per Indivisible Quantity | 1                                    |  |  |  |
| Shape Of Signaling Unit Head  | Round                                |  |  |  |
| Type Of Operator              | Left to centre spring return         |  |  |  |
| Operator Profile              | Red standard handle                  |  |  |  |
| Operator Position Information | 3 positions +/- 45°                  |  |  |  |
| Cap/Operator Or Lens Colour   | Red                                  |  |  |  |

## Complementary

| Cad Overall Width                  | 29 mm   |  |  |  |  |
|------------------------------------|---|--|--|--|--|
| Cad Overall Height                 | 29 mm   |  |  |  |  |
| Cad Overall Depth                  | 43 mm   |  |  |  |  |
| Net Weight                         | 0.036 kg  |  |  |  |  |
| Resistance To High Pressure Washer | 7000000 Pa at 55 °C, distance : 0.1 m   |  |  |  |  |
| Mechanical Durability              | 500000 cycles   |  |  |  |  |
| Electrical Composition Code        | M3 for <4 contacts using single blocks in front mounting with integral LED M6 for <2 contacts using single blocks in front mounting with integral LED and transformer M10 for <2 contacts using single blocks in front mounting with integral LED M4 for <4 contacts using single and double blocks in front mounting with integral LED |  |  |  |  |
| Device Presentation                | Basic element   |  |  |  |  |

## **Environment**

Protective Treatment

| Ambient Air Temperature For Storage                               | -4070 °C  |  |  |  |  |
|---|---|--|--|--|--|
| Ambient Air Temperature For<br>Operation                          | -4070 °C  |  |  |  |  |
| Overvoltage Category  | Class I conforming to IEC 60536   |  |  |  |  |
| Degree Of Protection IP66 conforming to IEC 60529 IP67 IP69 IP69K |   |  |  |  |  |
| Nema Degree Of Protection   | NEMA 13<br>NEMA 4X  |  |  |  |  |
| Ik Degree Of Protection   | IK04 conforming to IEC 50102  |  |  |  |  |
| Standards   | IEC 60947-5-5  JIS C8201-5-1  IEC 60947-5-4  CSA C22.2 No 14  IEC 60947-1  IEC 60947-5-1  UL 508  JIS C8201-1   |  |  |  |  |
| Product Certifications  | GL CSA UL listed DNV LROS (Lloyds register of shipping) BV  |  |  |  |  |
| Vibration Resistance  | 5 gn (f= 2500 Hz) conforming to IEC 60068-2-6   |  |  |  |  |
| Shock Resistance  | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |  |  |  |  |

# **Packing Units**

| Unit Type Of Package 1       | PCE       |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 3.3 cm    |
| Package 1 Width              | 4.8 cm    |
| Package 1 Length             | 5.2 cm    |
| Package 1 Weight             | 41 g      |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 5         |
| Package 2 Height             | 4.8 cm    |
| Package 2 Width              | 26.5 cm   |
| Package 2 Length             | 3.3 cm    |
| Package 2 Weight             | 205 g     |
| Unit Type Of Package 3       | S03       |
| Number Of Units In Package 3 | 250       |
| Package 3 Height             | 30 cm     |
| Package 3 Width              | 30 cm     |
| Package 3 Length             | 40 cm     |
| Package 3 Weight             | 11.008 kg |
|                              |           |

# **Contractual warranty**

Warranty

2 May 2024

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>9</b> | Toxic Heavy Metal Free     |     |
| <b>②</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

## **Certifications & Standards**


| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |

## **Product datasheet**

## **ZB4BK1743**

**Dimensions Drawings** 

## **Dimensions**



### **ZB4BK1743**

#### Mounting and Clearance


# Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connectors or on Printed Circuit Board

(1)

(2)

Connection by Screw Clamp Terminals or Plug-in



**Connection by Faston Connectors** 

(1) Diameter on finished panel or support

(3)


- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm  $_0^{+0.4}$  / 0.88 in.  $_0^{+0.016}$ )

(4)

- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.

#### Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

#### Panel Cut-outs (Viewed from Installer's Side)




**A:** 30 mm min. / 1.18 in. min. **B:** 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)


Dimensions in mm

## **ZB4BK1743**



**A:** 30 mm min. **B:** 40 mm min.

Dimensions in in.



**A:** 1.18 in. min. **B:** 1.57 in. min.

#### General Tolerances of the Panel and Printed Circuit Board


The cumulative tolerance must not exceed 0.3 mm / 0.012 in: T1 + T2 = 0.3 mm max.

#### **Installation Precautions**

- $_{\bullet}$  Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB4 BZ009: ± 2°30' (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ 006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB4 BZ079 fixing collar/pillar and its fixing screws:
  - $_{\circ}\;$  every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - o with each selector switch head (ZB4 BD•, ZB4 BJ•, ZB4 BG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.

#### **ZB4BK1743**



- (1) Panel
- (2) Printed circuit board

#### Mounting of Adapter (Socket) ZBZ 01•

- 1 2 elongated holes for ZBZ 006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ 01•
- 3 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ 01•


Dimensions An + 18.1 relate to the Ø 2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 holes for centring adapter ZBZ 01•.

## **Product datasheet**


## **ZB4BK1743**

**Technical Description** 

**Electrical Composition Corresponding to Code M3** 




## **Electrical Composition Corresponding to Code M4**



2 May 2024

## **Electrical Composition Corresponding to Codes M6 and P2**



## Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2




## Legend

Single contact



Double contact



Light block



Possible location



## Sequence of Contacts Fitted to 3-position Selector Switch Body

#### Position 315°



|          | Position | Тор    |        |           |        |
|----------|----------|--------|--------|-----------|--------|
| Push     | Position | Bottom |        | $\otimes$ |        |
|          | Location |        | Left   |           | Right  |
|          | State    |        | 1      |           | 0      |
| Contacts | N/O      |        | closed |           | open   |
|          | N/C      |        | open   |           | closed |

#### Position 0°



| Push     | Position | Тор    |        |           |        |
|----------|----------|--------|--------|-----------|--------|
|          |          | Bottom |        | $\otimes$ |        |
|          | Location |        | Left   |           | Right  |
|          | State    |        | 0      |           | 0      |
| Contacts | N/O      |        | open   |           | open   |
|          | N/C      |        | closed |           | closed |

#### Position 45°



| Push     | Position | Тор    |             |           |        |
|----------|----------|--------|-------------|-----------|--------|
|          |          | Bottom | $\triangle$ | $\otimes$ |        |
|          | Location |        | Left        |           | Right  |
|          | State    |        | 0           |           | 1      |
| Contacts | N/O      |        | open        |           | closed |
|          | N/C      |        | closed      |           | open   |