



# blue light block with body/fixing collar integral LED 24V

ZB4BVB64

! Discontinued on: 1 Jul 2020

EAN Code: 3389110892673

(!) Discontinued

#### Main

| Range Of Product              | Harmony XB4                        |
|-------------------------------|------------------------------------|
| Product Or Component Type     | Complete body/light block assembly |
| Device Short Name             | ZB4                                |
| Fixing Collar Material        | Zamak                              |
| Sale Per Indivisible Quantity | 1                                  |
| Connections - Terminals       | Plug-in connector                  |
| Light Source                  | Protected LED                      |
| Bulb Base                     | Integral LED                       |
| Light Source Colour           | Blue                               |
| [Us] Rated Supply Voltage     | 24 V AC/DC at 50/60 Hz             |

## Complementary

| Cad Overall Width                      | 30 mm   |
|--|---|
| Cad Overall Height                     | 47 mm   |
| Cad Overall Depth                      | 37 mm   |
| Terminals Description Iso N°1          | (X1-X2)PL   |
| Net Weight                             | 0.053 kg  |
| [Ui] Rated Insulation Voltage          | 250 V (pollution degree 3) conforming to EN 60947-1 |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV conforming to EN 60947-1                       |
| Signalling Type                        | Steady  |
| Supply Voltage Limits                  | 19.230 V DC<br>21.626.4 V AC                        |
| Current Consumption                    | 18 mA   |
| Service Life                           | 100000 h at rated voltage and 25 °C                 |
| Surge Withstand                        | 1 kV conforming to IEC 61000-4-5                    |

#### **Environment**

| <b>Protective Treatment</b>           | TH       |
|---------------------------------------|----------|
| Ambient Air Temperature For Storage   | -4070 °C |
| Ambient Air Temperature For Operation | -4070 °C |
| Floring of Objects Books attended     |          |

Electrical Shock Protection Class Class I conforming to IEC 60536

| Standards                             | CSA C22.2 No 14 EN/IEC 60947-5-4 JIS C8201-5-1 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL 508 JIS C8201-1  |  |
|---------------------------------------|---|--|
| Product Certifications                | UL listed<br>CSA  |  |
| Vibration Resistance                  | 5 gn (f= 2500 Hz) conforming to IEC 60068-2-6   |  |
| Shock Resistance                      | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |  |
| Resistance To Fast Transients         | 2 kV conforming to IEC 61000-4-4  |  |
| Resistance To Electromagnetic Fields  | 10 V/m conforming to IEC 61000-4-3  |  |
| Resistance To Electrostatic Discharge | 6 kV on contact (on metal parts) conforming to IEC 61000-2-6<br>8 kV in free air (in insulating parts) conforming to IEC 61000-2-6  |  |
| Electromagnetic Emission              | Class B conforming to IEC 55011   |  |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**


| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information   |

## **Product datasheet**

## ZB4BVB64

**Dimensions Drawings** 

## **Dimensions**




## ZB4BVB64


#### Mounting and Clearance

#### Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in **Connectors or on Printed Circuit Board** (1)







- (1) Diameter on finished panel or support
- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm  $_0^{+0.4}$  / 0.88 in.  $_0^{+0.016}$ )
- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.