Product datasheet

Specification





controller M221 16 IO transistor PNP Ethernet

TM221ME16T

EAN Code: 3606480611315

Main

Range Of Product	Modicon M221
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	24 V DC
Discrete Input Number	8, discrete input 4 fast input conforming to IEC 61131-2 Type 1
Analogue Input Number	2 at 010 V
Discrete Output Type	Transistor
Discrete Output Number	8 transistor 2 fast output
Discrete Output Voltage	24 V DC
Discrete Output Current	0.5 A

Complementary

oompromentary	
Discrete I/O Number	16
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)
Supply Voltage Limits	20.428.8 V
Inrush Current	35 A
Maximum Power Consumption In W	22.9 W at 24 V (with max number of I/O expansion module) 4 W at 24 V (without I/O expansion module)
Power Supply Output Current	0.52 A 5 V for expansion bus 0.49 A 24 V for expansion bus
Discrete Input Logic	Sink or source (positive/negative)
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Analogue Input Resolution	10 bits
Lsb Value	10 mV
Conversion Time	1 ms per channel + 1 controller cycle time for analogue input analog input
Permitted Overload On Inputs	+/- 30 V DC for 5 min (maximum) for analog input +/- 13 V DC (permanent) for analog input
Voltage State 1 Guaranteed	>= 15 V for input
Voltage State 0 Guaranteed	<= 5 V for input
Discrete Input Current	7 mA for discrete input 5 mA for fast input
Input Impedance	100 kOhm for analog input 3.4 kOhm for input 4.9 kOhm for fast input

Response Time	35 μs turn-off, 1215 terminal(s) for input 5 μs turn-on, 10, 11, 16, 17 terminal(s) for fast input 35 μs turn-on, other terminals terminal(s) for input 5 μs turn-off, 10, 11, 16, 17 terminal(s) for fast input 100 μs turn-off, other terminals terminal(s) for input 5 μs turn-on, turn-off, Q0Q1 terminal(s) for output 50 μs turn-on, turn-off, Q2Q3 terminal(s) for output 300 μs turn-on, turn-off, other terminals terminal(s) for output	
Configurable Filtering Time	0 ms for input 3 ms for input 12 ms for input	
Discrete Output Logic	Positive logic (source)	
Maximum Current Per Output Common	4 A	
Output Frequency	100 kHz for fast output (PWM/PLS mode) at Q0Q1 5 kHz for output at Q2Q3 0.1 kHz for output at Q4Q6	
Absolute Accuracy Error	+/- 1 % of full scale for analog input	
Maximum Leakage Current	0.1 mA for transistor output	
Maximum Voltage Drop	<1 V	
Mechanical Durability	20000000 cycles for transistor output	
Maximum Tungsten Load	<12 W for output and fast output	
Protection Type	Short-circuit and overload protection with automatic reset Short-circuit protection on output Overload and short-circuit protection at 1 A	
Reset Time	1 s automatic reset	
Memory Capacity	256 kB for user application and data RAM with 10000 instructions 256 kB for internal variables RAM	
Data Backed Up	256 kB built-in flash memory for backup of application and data	
Data Storage Equipment	2 GB SD card (optional)	
Battery Type	BR2032 or CR2032X lithium non-rechargeable	
Backup Time	1 year at 25 °C (by interruption of power supply)	
Execution Time For 1 Kinstruction	me For 1 Kinstruction 0.3 ms for event and periodic task 0.7 ms for other instruction	
Execution Time Per Instruction	0.2 μs Boolean	
Exct Time For Event Task	60 μs response time	
Application Structure	1 cyclic auxiliary task 1 configurable freewheeling/cyclic master task 8 interrupt tasks	
Maximum Size Of Object Areas	512 %M memory bits 512 %KW constant words 8000 %MW memory words 255 %TM timers 255 %C counters	
Realtime Clock	With	
Clock Drift	<= 30 s/month at 25 °C	
Regulation Loop	Adjustable PID regulator up to 14 simultaneous loops	
Positioning Functions	Position PTO 2 axe(s)pulse/direction mode (100 kHz) Position PTO 1 axe(s)CW/CCW mode (100 kHz)	
Function Available	PLS Frequency generator PWM	
Counting Input Number	4 fast input (HSC mode) at 100 kHz 32 bits	

Counter Function Pulse/direction A/B Single phase		
Integrated Connection Type	USB port with mini B USB 2.0 connector Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface Ethernet with RJ45 connector	
Supply	(serial 1)serial link supply: 5 V, <200 mA	
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for USB	
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network Ethernet	
Port Ethernet	10BASE-T/100BASE-TX 1 port with 100 m copper cable	
Communication Service	DHCP client Ethernet/IP adapter Modbus TCP server Modbus TCP slave device Modbus TCP client	
Local Signalling	1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED per channel (green) for I/O state 1 LED (green) for SL Ethernet network activity (green) for ACT Ethernet network link (yellow) for Link (Link Status)	
Electrical Connection	terminal block, 3 terminal(s) for connecting the 24 V DC power supply connector, 4 terminal(s) for analogue inputs Mini B USB 2.0 connector for a programming terminal removable screw terminal block, 10 terminal(s) for inputs removable screw terminal block, 11 terminal(s) for outputs	
Maximum Cable Distance Between Devices	Shielded cable: <10 m for fast input Unshielded cable: <30 m for output Unshielded cable: <30 m for digital input Unshielded cable: <1 m for analog input Shielded cable: <3 m for fast output	
Insulation	Between input and internal logic at 500 V AC Between fast input and internal logic at 500 V AC Non-insulated between inputs Between output and internal logic at 500 V AC Non-insulated between analogue input and internal logic Non-insulated between analogue inputs	
Marking	CE	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
Depth	70 mm	
Width	70 mm	
Net Weight	0.264 kg	

Environment

Standards IEC 61131-2

UL 508 CAN/CSA C22.2 No. 213 IACS E10 ANSI/ISA 12-12-01

Life Is On Schneider 18 May 2024

Product Certifications	RCM	
	ABS	
	cULus	
	DNV-GL	
	EAC	
	LR	
	CE	
	UKCA	
	cULus HazLoc	
Environmental Characteristic	Ordinary and hazardous location	
Resistance To Electrostatic	8 kV in air conforming to IEC 61000-4-2	
Discharge	4 kV on contact conforming to IEC 61000-4-2	
Resistance To Electromagnetic	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3	
Fields	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3	
	1 V/m 22.7 GHz conforming to IEC 61000-4-3	
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8	
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4	
	2 kV (relay output) conforming to IEC 61000-4-4	
	1 kV (I/O) conforming to IEC 61000-4-4	
	1 kV (Ethernet line) conforming to IEC 61000-4-4	
	1 kV (serial link) conforming to IEC 61000-4-4	
Surge Withstand	2 kV nower lines (AC) common mode conforming to IEC 61000 4.5	
Cargo Willistand	2 kV power lines (AC) common mode conforming to IEC 61000-4-5	
	2 kV relay output common mode conforming to IEC 61000-4-5 1 kV I/O common mode conforming to IEC 61000-4-5	
	1 kV shielded cable common mode conforming to IEC 61000-4-5	
	0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5	
	1 kV power lines (AC) differential mode conforming to IEC 61000-4-5	
	1 kV relay output differential mode conforming to IEC 61000-4-5	
	0.5 kV power lines (DC) common mode conforming to IEC 61000-4-5	
Resistance To Conducted	10 V 0.1580 MHz conforming to IEC 61000-4-6	
Disturbances	3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL)	
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to	
	Marine specification (LR, ABS, DNV, GL)	
Electromagnetic Emission	Conducted emissions - test level: 79 dBµV/m QP/66 dBµV/m AV (power lines (AC))	
Licotromagnetto Limeolon	at 0.150.5 MHz conforming to IEC 55011	
	Conducted emissions - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC))	
	at 0.5300 MHz conforming to IEC 55011	
	Conducted emissions - test level: 12069 dBµV/m QP (power lines) at 10150 kHz	
	conforming to IEC 55011	
	Conducted emissions - test level: 63 dBµV/m QP (power lines) at 1.530 MHz	
	conforming to IEC 55011	
	Radiated emissions - test level: 40 dBµV/m QP class A (10 m) at 30230 MHz	
	conforming to IEC 55011	
	Conducted emissions - test level: 7963 dBµV/m QP (power lines) at 1501500	
	kHz conforming to IEC 55011	
	Radiated emissions - test level: 47 dBµV/m QP class A (10 m) at 2001000 MHz	
	conforming to IEC 55011	
Immunity To Microbreaks	ıks 10 ms	
Ambient Air Temperature For	-1055 °C (horizontal installation)	
Operation	-1035 °C (vertical installation)	
Ambient Air Temperature For Storage	-2570 °C	
Relative Humidity	1095 %, without condensation (in operation)	
Relative Humany	1095 %, without condensation (in operation)	
Ip Degree Of Protection	IP20 with protective cover in place	
Pollution Degree	<= 2	
Operating Altitude	02000 m	
Storage Altitude	03000 m	
Vibration Posistance	2.5 mm at 5 0.4 lb an armount in land	
Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail	
	3.5 mm at 58.4 Hz on panel mounting	
	1 gn at 8.4150 Hz on symmetrical rail	
	1 gn at 8.4150 Hz on panel mounting	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.8 cm
Package 1 Width	10.0 cm
Package 1 Length	12.6 cm
Package 1 Weight	430.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	24
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.966 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	105.0 cm
Package 3 Width	120.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	142 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Environmental Disclosure	Product Environmental Profile	
China Rohs Regulation	China RoHS declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
Reach Regulation	REACh Declaration	


Product datasheet


TM221ME16T

Dimensions Drawings

Dimensions

18 May 2024






Product datasheet


TM221ME16T

Mounting and Clearance

Mounting on a Rail




Direct Mounting on a Panel Surface




(1) Install a mounting strip


Mounting

Correct Mounting Position








Acceptable Mounting Position




Incorrect Mounting Position









Clearance





Connections and Schema

Digital Inputs



(1) The COM0 terminals are connected internally.


A: Sink wiring (positive logic).

B: Source wiring (negative logic).




lx I0, I1, I6, I7

Digital Outputs





- (*) Type T fuse
- (1) The V+ terminals are connected internally.



Qx Q0, Q1

Analog Inputs







The (-) poles are connected internally.

Pin	Wire Color
AN0 / AN1	Red
0 V	Black


Ethernet Connection




Pin N °	Signal
1	TD+
2	TD-
3	RD+
4	-
5	-
6	RD-
7	_
8	_



USB Mini-B Connection



SL1 Connection




SL1

Ν°	RS 232	RS 485
1	RxD	N.C.
2	TxD	N.C.
3	RTS	N.C.
4	N.C.	D1
5	N.C.	D0
6	стѕ	N.C.
7	N.C.*	5 Vdc
8	Common	Common

N.C.: not connected


 $[\]ensuremath{^*}$: 5 Vdc delivered by the controller. Do not connect.



Performance Curves

Derating Curves


Embedded Digital Inputs



X: Ambient temperature

Y: Input simultaneous ON ratio

Embedded Digital Outputs



X: Ambient temperature

Y: Output simultaneous ON ratio