Specifications





controller M241 24 IO transistor PNP Ethernet CAN master

TM241CEC24T

EAN Code: 3606480611117

Main

Range Of Product	Modicon M241	
Product Or Component Type	Logic controller	
[Us] Rated Supply Voltage	24 V DC	
Discrete Input Number	14, discrete input 8 fast input conforming to IEC 61131-2 Type 1	
Discrete Output Type	Transistor	
Discrete Output Number	10 transistor 4 fast output	
Discrete Output Voltage	24 V DC for transistor output	
Discrete Output Current	0.5 A for transistor output (Q0Q9) 0.1 A for fast output (PTO mode) (Q0Q3)	

Complementary

Discrete I/O Number	24		
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)		
Supply Voltage Limits	20.428.8 V		
Inrush Current	50 A		
Power Consumption In W	32.640.4 W (with max number of I/O expansion module)		
Discrete Input Logic	Sink or source		
Discrete Input Voltage	24 V		
Discrete Input Voltage Type	DC		
Voltage State 1 Guaranteed	>= 15 V for input		
Voltage State 0 Guaranteed	<= 5 V for input		
Discrete Input Current	5 mA for input 10.7 mA for fast input		
Input Impedance	4.7 kOhm for input 2.81 kOhm for fast input		
Response Time	50 μs turn-on, 10113 terminal(s) for input 50 μs turn-off, 10113 terminal(s) for input <= 2 μs turn-on, 1017 terminal(s) for fast input <= 2 μs turn-off, 1017 terminal(s) for fast input <= 34 μs turn-on, 2029 terminal(s) for output <= 250 μs turn-off, 2029 terminal(s) for output <= 2 μs turn-on, 2029 terminal(s) for fast output		

<= 2 µs turn-off, Q0...Q3 terminal(s) for fast output

Configurable Filtering Time	1 µs for fast input	
	12 ms for fast input	
	0 ms for input 1 ms for input	
	4 ms for input	
	12 ms for input	
Discrete Output Logic	Positive logic (source)	
Output Voltage Limits	30 V DC	
Maximum Current Per Output	2 A with Q0Q3 for fast output	
Common	2 A with Q4Q7 for output 1 A with Q8Q9 for output	
Maximum Output Frequency	·	
	20 kHz for fast output (PWM mode) 100 kHz for fast output (PLS mode)	
	1 kHz for output	
Accuracy	+/- 0.1 % at 0.020.1 kHz for fast output	
	+/- 1 % at 0.11 kHz for fast output	
Maximum Leakage Current	5 µA for output	
Maximum Voltage Drop	<1 V	
Maximum Tungsten Load	<2.4 W	
Protection Type	Short-circuit protection	
	Short-circuit and overload protection with automatic reset	
	Reverse polarity protection for fast output	
Reset Time	10 ms automatic reset output	
	12 s automatic reset fast output	
Memory Capacity	64 MB for system memory RAM	
Data Backed Up	128 MB built-in flash memory for backup of user programs	
Data Storage Equipment	<= 16 GB SD card (optional)	
Battery Type	BR2032 lithium non-rechargeable, battery life: 4 year(s)	
Backup Time	2 years at 25 °C	
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task	
	0.7 ms for other instruction	
Application Structure	8 external event tasks	
	4 cyclic master tasks	
	3 cyclic master tasks + 1 freewheeling task 8 event tasks	
Realtime Clock	With	
Clock Drift	<= 60 s/month at 25 °C	
Positioning Functions	PTO function 4 channel(c) (positioning frequency: 100 kHz)	
r osidoning r uncdons	PTO function 4 channel(s) (positioning frequency: 100 kHz) PTO function 4 channel(s) for transistor output (positioning frequency: 1 kHz)	
Counting Input Number	4 fast input (HSC mode) at 200 kHz	
	14 standard input at 1 kHz	
Control Signal Type	A/B at 100 kHz for fast input (HSC mode)	
	Pulse/direction at 200 kHz for fast input (HSC mode)	
	Single phase at 200 kHz for fast input (HSC mode)	
Integrated Connection Type	Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface	
	Non isolated serial link serial 2 with removable screw terminal block connector and	
	RS485 interface	
	USB port with mini B USB 2.0 connector Ethernet with RJ45 connector	
	CANopen J1939 with male SUB-D 9 connector	
Supply	(serial 1)serial link supply: 5 V, <200 mA	

Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for bus length of 3 m for USB		
	10/100 Mbit/s for Ethernet		
	1000 kbit/s for bus length of 20 m for CANopen 800 kbit/s for bus length of 40 m for CANopen		
	500 kbit/s for bus length of 100 m for CANopen		
	250 kbit/s for bus length of 250 m for CANopen		
	125 kbit/s for bus length of 500 m for CANopen 50 kbit/s for bus length of 1000 m for CANopen		
	20 kbit/s for bus length of 2500 m for CANopen		
Communication Port Protocol	Non isolated serial link: Modbus master/slave		
Port Ethernet	10BASE-T/100BASE-TX - 1 port(s) copper cable		
Ethernet Services	SNMP client/server		
	Modbus TCP slave device Modbus TCP server		
	Modbus TCP client		
	IEC VAR ACCESS		
	FTP client/server		
	SQL client		
	DHCP client Ethernet/IP adapter		
	Send and receive email from the controller based on TCP/UDP library		
	Web server (WebVisu & XWeb system)		
	OPC UA server		
	DNS client		
Local Signalling	1 LED (green) for PWR		
	1 LED (green) for RUN 1 LED (red) for module error (ERR)		
	1 LED (red) for I/O error (I/O)		
	1 LED (green) for SD card access (SD)		
	1 LED (red) for BAT		
	1 LED (green) for SL1		
	1 LED (green) for SL2 1 LED (red) for bus fault on TM4 (TM4)		
	1 LED per channel (green) for I/O state		
	1 LED (green) for Ethernet port activity		
	1 LED (green) for CANopen run		
	1 LED (green) for CANopen error		
Electrical Connection	removable screw terminal blockfor inputs and outputs (pitch 5.08 mm) removable screw terminal blockfor connecting the 24 V DC power supply (pitch 5.08 mm)		
Maximum Cable Distance	Unshielded cable: <50 m for input		
Between Devices	Shielded cable: <10 m for fast input		
	Unshielded cable: <50 m for output Shielded cable: <3 m for fast output		
	·		
Insulation	Between supply and internal logic at 500 V AC Non-insulated between supply and ground		
	Between input and internal logic at 500 V AC		
	Non-insulated between inputs		
	Between fast input and internal logic at 500 V AC		
	Between output and internal logic at 500 V AC Non-insulated between outputs		
	Between fast output and internal logic at 500 V AC		
Marking	CE		
Surge Withstand	1 kV power lines (DC) common mode conforming to IEC 61000-4-5		
	1 kV shielded cable common mode conforming to IEC 61000-4-5		
	0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5		
	1 kV relay output differential mode conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5		
	1 kV transistor output common mode conforming to IEC 61000-4-5		
Web Services	Web server		
Maximum Number Of	16 Ethernet/IP device		
Connections	8 Modbus server		
Canopen Feature Profile	DS 301 V4.02 DR 303-1		
Number Of Server Device(S)	63 CANopen:		
(-)	····		

Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
Depth	95 mm	
Width	150 mm	
Net Weight	0.53 kg	

Environment

Standards	ANSI/ISA 12-12-01 CSA C22.2 No 142 CSA C22.2 No 213 IEC 61131-2:2007 Marine specification (LR, ABS, DNV, GL) UL 508	
Product Certifications	RCM cULus CE UKCA DNV-GL ABS LR	
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2	
Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3	
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4 1 kV (Ethernet line) conforming to IEC 61000-4-4 1 kV (serial link) conforming to IEC 61000-4-4 1 kV (input) conforming to IEC 61000-4-4 1 kV (transistor output) conforming to IEC 61000-4-4	
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL) 10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)	
Electromagnetic Emission	Conducted emissions - test level: 12069 dBµV/m QP (power lines) at 10150 kHz conforming to IEC 55011 Conducted emissions - test level: 63 dBµV/m QP (power lines) at 1.530 MHz conforming to IEC 55011 Radiated emissions - test level: 40 dBµV/m QP class A at 30230 MHz conforming to IEC 55011 Conducted emissions - test level: 7963 dBµV/m QP (power lines) at 1501500 kHz conforming to IEC 55011 Radiated emissions - test level: 47 dBµV/m QP class A at 2301000 MHz conforming to IEC 55011	
Immunity To Microbreaks	10 ms	
Ambient Air Temperature For Operation	-10…50 °C (vertical installation) -10…55 °C (horizontal installation)	
Ambient Air Temperature For Storage	-2570 °C	
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)	
Ip Degree Of Protection	IP20 with protective cover in place	
Pollution Degree	2	
Operating Altitude	02000 m	
Storage Altitude	03000 m	

Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail 3 gn at 8.4150 Hz on symmetrical rail 3.5 mm at 58.4 Hz on panel mounting 3 gn at 8.4150 Hz on panel mounting	
	3 gn at 8.4…150 Hz on panel mounting	

Shock Resistance

15 gn for 11 ms

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.3 cm
Package 1 Width	13.115 cm
Package 1 Length	18.729 cm
Package 1 Weight	661.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.16 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	64
Package 3 Height	75.0 cm
Package 3 Width	40.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	59 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance





Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

Dimensions Drawings


Dimensions







Mounting and Clearance

Clearance






Mounting Position




Acceptable Mounting




NOTE: Expansion modules must be mounted above the logic controller.

Incorrect Mounting



Direct Mounting On a Panel Surface


Mounting Hole Layout



Connections and Schema

Digital Inputs

Wiring Diagram




- (*): Type T fuse
- (1): The COM0, COM1 and COM2 terminals are not connected internally
- (A): Sink wiring (positive logic)
- (B): Source wiring (negative logic)

Fast Input Wiring (I0...I7)



Fast Transistor Outputs


Wiring Diagram



(*): 2 A fast-blow fuse

Transistor Outputs

Wiring Diagram




(*): Type T fuse


(1): The V1+ and V2+ terminals are not connected internally.

(2): The V1- and V2- terminals are not connected internally.

USB Mini-B Connection




Ethernet Connection to a PC



CANopen Connection

Wiring Diagram



Pin	Signal	Description	Marking	Color of Cable
1	Not used	Reserved	NC	red
2	CAN_H	CAN_H bus line (dominant high)	CAN_H	white
3	CAN_SHLD	Optional CAN shield	Shield	-
4	CAN_L	CAN_L bus line (dominant low)	CAN_L	blue
5	CAN_GND	CAN Ground	GND	black